

Lead Time Bulletin

August 19, 2022 • Volume 2022 • Issue 16

TOTO®

Page 1 of 2

Category	Item Number	Description	LT (wks) as of 08/19/22	LT (wks) as of 08/05/22
1-PC TOILET	MS614124CEF#51	CARLYLE® II 1-PC TOILET, 1.28 GPF, ELONG. FRONT, W/ SS124 SEAT, UH, ADA COMPLIANT, 28-1/4" X 16-1/2" X 28-3/4"	9	11
	MS642124CEF#51	NEXUS® 1-PC TOILET, 1.28 GPF, ELONG. FRONT, W/ SS124 SEAT, UH, ADA COMPLIANT, 28-9/16" X 17-1/2" X 27"	11	11
	MS642124CUF#51	NEXUS 1-PC TOILET, 1.0 GPF, ELONG. FRONT, W/ SS124 SEAT, ADA COMPLIANT, UH, 28-9/16" X 17-1/2" X 27"	11	11
	MS644124CEF#51	CAROLINA® II 1-PC TOILET, 1.28 GPF, ELONG. FRONT, W/ SS124 SEAT, UH, ADA COMPLIANT, 28-5/16" X 17-1/8" X 25-5/8"	11	13
	MS854114EG#01	ECO ULTRAMAX® 1-PC TOILET, 1.28 GPF, W/ CEFIONTECT®, W/ SS114 SEAT, 28" X 16-1/2" X 27-1/8"	5	7
2-PC TOILET	C453CUFG#12	DRAKE® II 2-PC TOILET, ROUND FRONT BOWL ONLY, W/ CEFIONTECT, UH, 26-1/2" X 16" X 30"	9	7
	C754EF#12	DARTMOUTH® ELONGATED BOWL, 28-1/2" X 20-5/8" X 32-1/2"	9	7
BATHTUB	ABY782P#01YCP	CLAYTON® SOAKER, W/ GRAB BAR, LEFT DRAIN, 60" X 32" X 24-1/2"	18	12
	ABY782Q#01YCP	CLAYTON SOAKER, W/ GRAB BAR, RIGHT DRAIN, 60" X 32" X 24-1/2"	18	12
	PJY1724PWEU#GW	FLOTATION FREESTANDING SQUARE BATHTUB 66-15/16" X 31-1/2" X 22-1/4"	14	13
	PJYD2200PWEU#GW	FLOTATION TUB W/ ZERO DIMENSION® 86-5/8" X 41-5/16" X 30-11/16"	16	13
COMMERCIAL TOILET	CT705ULNG#01	COMMERCIAL FLUSHOMETER HIGH-EFFICIENCY TOILET, 1.0 GPF, W/ CEFIONTECT, ADA COMPLIANT	9	9
	CT705ULNGX#01	COMMERCIAL FLUSHOMETER HIGH-EFFICIENCY TOILET, 1.0 GPF, W/ CEFIONTECT, FOR RECLAIMED WATER, ADA COMPLIANT	12	
EFV	TET1GA32#CP	ECOPOWER® TOILET FLUSH VALVE AND VACUUM BREAKER SET, 1.6 GPF, ADA COMPLIANT	7	9
	TET1GAR#CP	ECOPOWER HIGH-EFFICIENCY TOILET FLUSH VALVE ONLY, 1.6 GPF	7	
	TET1LA32#CP	ECOPOWER HIGH-EFFICIENCY TOILET FLUSH VALVE AND VACUUM BREAKER SET, 1.28 GPF, ADA COMPLIANT	12	9
	TET1LAX32#CP	ECOPOWER HIGH-EFFICIENCY TOILET FLUSH VALVE AND VACUUM BREAKER SET, 1.28 GPF, FOR RECLAIMED WATER, ADA COMPLIANT	12	22
	TET1UA32#CP	ECOPOWER ULTRA HIGH-EFFICIENCY TOILET FLUSH VALVE AND VACUUM BREAKER SET, 1.0 GPF, ADA COMPLIANT	7	18
	TET1UAX32#CP	ECOPOWER HIGH-EFFICIENCY TOILET FLUSH VALVE AND VACUUM BREAKER SET, 1.0 GPF, FOR RECLAIMED WATER, ADA COMPLIANT	12	35
	TET3LA31#SS	ECOPOWER HIGH-EFFICIENCY TOILET FLUSH VALVE AND VACUUM BREAKER SET, 1.28 GPF, FOR WALL-HUNG TOILET WITH 1-1/2" BACK SPUD INLET, ADA COMPLIANT	20	22
	TET3LA33#SS	ECOPOWER HIGH-EFFICIENCY TOILET FLUSH VALVE AND VACUUM BREAKER SET, 1.28 GPF, FOR FLOOR-MOUNT TOILET WITH 1-1/2" BACK SPUD INLET, ADA COMPLIANT	25	
ELECTRONIC FAUCETRY	TELC101R-D10E	CONTROLLER, 0.18 GPC, 10 SECS ON DEMAND	8	10
	TLE23007U1#CP	LIBELLA® TOUCHLESS SEMI-VESSEL SPOUT, 0.5 GPM, 10 SEC ON-DEMAND	9	
	TLE24008U1#CP	TOUCHLESS GOOSENECK VESSEL SPOUT, 0.5 GPM, 0.08 GPC, 10 SEC ON-DEMAND	11	10
	TLE24008U3#CP	TOUCHLESS GOOSENECK VESSEL SPOUT, 0.5 GPM, 0.17 GPC, 20 SEC ON-DEMAND	26	28
	TLE25003U2#CP	AXIOM® TOUCHLESS L SPOUT - VESSEL, 0.35 GPM, 20 SEC ON-DEMAND	21	28
	TLE26001U2#CP	HELIX® TOUCHLESS SPOUT, 0.35 GPM, 20 SEC ON-DEMAND	9	
	TLE26005U2#CP	HELIX TOUCHLESS WALL-MOUNT SPOUT, 0.35 GPM, 20 SEC ON-DEMAND	31	
HAND DRYER	HDR111#SS	CLEAN DRY HIGH SPEED HAND DRYER, ADA COMPLIANT	7	9

1. This report presents lead times, at the time of publication, for those SKU's that have lead times of 5 weeks or more.
2. The lead time shown here is for reference only and merely represents the static and current lead time status based on the current open orders, backorders and production schedule. Lead times can be subject to frequent change depending on the volume of additional demand in the future or other factors without notice. Therefore, TOTO USA specifically disclaims any liability or responsibility whatsoever resulting directly or indirectly from the lead time guides.
3. To check status of your TOTO order – use TOTO Sales: <http://totoe2w.toto.usa.com> or TOTO Customer Service: 888-295-8134

Lead Time Bulletin

August 19, 2022 • Volume 2022 • Issue 16

TOTO®

Page 2 of 2

Category	Item Number	Description	LT (wks) as of 08/19/22	LT (wks) as of 08/05/22
LAVATORY	LT1535G#01	RECTANGLE UNDERCOUNTER LAVATORY, W/ CEFIONTECT®, FRONT OVERFLOW, ADA COMPLIANT, 17-11/16" X 13"	7	9
	LT191G#11	RECTANGLE UNDERCOUNTER LAVATORY, W/ CEFIONTECT, REAR OVERFLOW, ADA COMPLIANT, 20-1/2" X 12-3/8"	7	7
	LT241G#03	SUPREME® PEDESTAL LAVATORY, WITH CEFIONTECT, SINGLE-HOLE FAUCET MOUNT, UH, 22-7/8" X 19-5/8"	9	9
	LT426G#01	ARVINA® RECTANGLE VESSEL LAVATORY, W/ CEFIONTECT, FRONT OVERFLOW, ADA COMPLIANT, 23-5/8" X 14-15/16" X 2-3/4"	20	18
	LT476GR#01	KIWAMI® RECTANGLE VESSEL LAVATORY, W/ CEFIONTECT, FRONT OVERFLOW, ADA COMPLIANT, 23-5/8" X 15" X 2-3/4"	18	13
	LT579G#12	RENDEZVOUS® UNDERCOUNTER LAVATORY, W/ CEFIONTECT, FRONT OVERFLOW, ADA COMPLIANT, 17" X 14"	11	
	LT587#01	UNDERCOUNTER LAVATORY, FRONT OVERFLOW, ADA COMPLIANT, 19" X 15"	9	9
	LT754.8#01	WHITNEY® PEDESTAL LAVATORY, 8" CENTERS, 25" X 19"	7	9
	LT780.4#01	CLAYTON® LAVATORY ONLY, 4" CENTERS, 27" X 19-5/8"	7	9
	LT781.8#01	CLAYTON SELF-RIMMING LAVATORY, REAR OVERFLOW, 8" CENTERS, ADA COMPLIANT, 25" X 18-1/4"	9	
RESIDENTIAL FAUCETRY	TBN01001U	MINI UNIT ROUGH-IN BOX	7	9
	TBV02404U#BN	THERMOSTATIC MIXING VALVE WITH TWO-WAY DIVERTER, TRIM - SQUARE, FOR USE WITH MINI UNIT	17	19
	TBV02406U#CP	THERMOSTATIC MIXING VALVE 2-FUNCTION TRIM, FOR USE WITH MINI UNIT	7	9
	TBW01016U#BN	SLIDE BAR - ROUND 24"	9	6
	TLG01304U#BN	GO SINGLE-HANDLE FAUCET - SEMI-VESSEL, 1.2 GPM, W/ LEVER HANDLE, ADA COMPLIANT	7	9
	TLG01310U#BN	GO WALL-MOUNT FAUCET - SHORT, 1.2 GPM, W/ LEVER HANDLE, ADA COMPLIANT	10	14
	TLG02307U#CP	GR SINGLE-HANDLE FAUCET - VESSEL, 1.2 GPM, W/ LEVER HANDLE	7	9
SOAP	TSFB1-GS	SOAP, 1 GALLON, PACKAGE OF 4, GREENSEAL	11	7
	TSFG1	SOAP, 1 GALLON, PACKAGE OF 4, ANTIBACTERIAL	11	7
URINAL	UT445UV#01	COMMERCIAL WASHOUT ULTRA HIGH-EFFICIENCY URINAL, ADA COMPLIANT	9	6
WALL-HUNG TOILET	CT426CFGT40#01	AP WALL- HUNG ELONG. FRONT BOWL ONLY, W/ T40 CONCEALED CONNECTION, W/ CEFIONTECT, UH	5	5

1. This report presents lead times, at the time of publication, for those SKU's that have lead times of 5 weeks or more.
2. The lead time shown here is for reference only and merely represents the static and current lead time status based on the current open orders, backorders and production schedule. Lead times can be subject to frequent change depending on the volume of additional demand in the future or other factors without notice. Therefore, TOTO USA specifically disclaims any liability or responsibility whatsoever resulting directly or indirectly from the lead time guides.
3. To check status of your TOTO order – use TOTO Sales: <http://totoe2w.toto.usa.com> or TOTO Customer Service: 888-295-8134

888-295-8134
www.totousa.com
 © 2022 TOTO U.S.A.